



SENTRY RC-200 RESIN COLUMN SENTRY RC-400 RESIN COLUMN

Cation Exchange Resin Columns

SAMPLE CONDITIONING

The Sentry® RC-200 and RC-400 refillable ion exchange resin columns make resin replacement easy and economical, minimizing channeling and achieving a higher resin efficiency than competitive columns with inefficient column diameters.

MODELS

RC-200

RC-400

BENEFITS

The RC-200 and RC-400 refillable ion exchange resin columns are designed to minimize the column's dead volume, assuring highly representative sampling, and meet the demands of special applications, such as the need for large volumes of resin to extend the time between resin replacement or regeneration.

The resin columns have removable caps at both ends of the column to assist in refilling or regeneration of the resin. Additionally, porous discs are installed at both ends to contain the resin, assist in flow distribution and reduce channeling.


FEATURES

- Refillable, clear plastic column makes resin replacement economical and easy
- Provides optimum fluid velocity with increased resin efficiency
- Designed especially for flow rates common to water chemistry analyzers
- Minimizes lag time required to detect chemical upset
- No PVC used; wetted materials will not leach chlorides or plasticizers
- End fittings are 1/8-inch quick disconnects



Sample. Monitor. Measure.
SENTRY
Any Application. Anywhere.

	DIM A	DIM B	DIM C
RC-200	13¼" (337 mm)	8⅞" (222mm)	3⅞" (79 mm)
RC-400	23¾" (598 mm)	18⅞" (481 mm)	3⅞" (79 mm)



SPECIFICATIONS

operating temperature	180°F (82°C) maximum	
operating pressure	100 psig at 100°F (7 barg at 38°C); 60 psig at 180°F (4 barg at 82°C)	
flow	200 cc/min recommended; 500 cc/min maximum	
wetted materials	polycarbonate, polypropylene, acetal	
resin	cation resin with color-indicating dye	
resin volume	RC-200: 0.040 ft. ³ (1130 cc)	RC-400: 0.080 ft. ³ (2260 cc)
cation capacity	RC-200: 2000 grains as CaCO ₃	RC-400: 4000 grains as CaCO ₃
weight	column + resin: RC-200: 4.25 lb. (2 kg.)	RC-400: 6.5 lb. (3 kg.)

PART NUMBERS

	RC-200	RC-400
resin column with initial change of resin, mounting brackets, and two sets of quick disconnects	7-04037A	7-00816B
cation resin refill bag (0.022 ft. ³)	2-03972A (2 required)	2-03972A (4 required)
corrosion-proof quick disconnect mounting bracket	4-05263A	4-05263A
standard cap	2-07030C	2-07030C
kit (includes two each O-rings and porous disks)	6-02503D	6-02503D

sentry-equip.com

966 Blue Ribbon Circle North, Oconomowoc, WI 53066 U.S.A. | +1-262-567-7256 | sales@sentry-equip.com

© 2015 Sentry Equipment Corp. All rights reserved. All product and company names are property of their respective owners. It is solely the responsibility of end users, through their own testing and analysis, to select products and materials suitable for their specific application requirements, ensure they are properly installed, safely applied and properly maintained, and to limit their use to their intended purpose. Improper selection, installation or use may result in personal injury or property damage.

S-SW-SPS-00141-3 2-16



COMPANY WITH
QUALITY SYSTEM
CERTIFIED BY DNV GL
= ISO 9001 =